



## Metal Clad Cable Termination Fittings & Accessories

### T&B Catalog Number:

STX050-464

### UPC Number:

78621090475

### Status:

Active

### Description:

Star Teck XP hazardous location aluminum jacketed cable fitting hub size 1/2 inch Range over jacket 0.600-0.760 inch.

### Features

Sealing chamber is easier to fill, requires less sealing compound, saves time and material.

Flame path is optimally designed to allow for easy insertion into hub, quick-turn lock.

Union features twist-on action; red color for high visibility.

Exclusive power grip, provides grip that is high up on cable armor non-magnetic stainless steel power grip grounding ring.

Low profile gland nut.

### Application

Provides means for passing armored, metal clad, jacketed cable through a bulkhead or enclosure in hazardous areas. (these fittings are suitable for hazardous areas when used with T&B sealing compound).

Form a mechanical grip and water and/or oil-resistant termination.

Provide grounding continuity of cable armor.

### General

Material Aluminum

Strip Length (inches) 1 1/4

B Overall (inches) 2.530

C Maximum Aluminum (inches) 1.630

Sealing Compound Required-Putty (grams) 7

Sealing Compound Required-Liquid (cc) 4

### Dimension Information

Hub Size (inches) 1/2

A2:Throat Diameter Minimum (wo/Armor Stop) 0.485

Range Over Jacket -Minimum (inches) 0.600

Range Over Jacket -Maximum (inches) 0.760

Range Over Armor -Minimum (inches) 0.490

Range Over Armor -Maximum (inches) 0.680

Strip Length (inches) 1 1/4

### Specifications

3dmodel Available on Website

### Packaging

T&B Order Multiple 2

T&B Inner Pack 2

Package in Units 20

T&B Sold in UOM Each

T&B Weight Per UOM	31.08 lbs. per 100
--------------------	--------------------

## Application Support

Product Specifications & Overview	Available on Website
-----------------------------------	----------------------

## Notes

*Note	UL Listed watertight NEMA Type 6P
-------	-----------------------------------

**Note	1/2" Fittings do not have a removable armor stop.
--------	---

## Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:

E 82038

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)