



S9570

4.5W CTC/LED/27K/120V
4.5 watt C11 LED; Clear; Candelabra base; 2700K; 450 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.

Compatible Dimmers

- Cooper TAL06P-C1
- Leviton DSE06
- Lutron NTCL-250



S9570

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9570	045923095702	120	4.5	40W	>0.70	C11	Candelabra

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E12	4.5W CTC/LED/27K/120V	Dimmable	Clear	4-5/16"	1.38"	450	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant
2700	Warm White	80	360	-20°C (-4°F) to a maximum of +45°C (113°F)	24/6	Box	Yes

UL or ETL Listed		UL Classification			Warranty		
Yes		cULus - Damp Location Rated			3 Year Limited		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051