



# S9382

6.5MR16/LED/40'/27K/120V/GU10  
 6.5 watt; LED MR16 LED; 2700K; 40' beam spread; GU10 base; 120 volts

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable
- UL approved for totally enclosed fixtures

### Compatible Dimmers

- Cooper DAL06P-C2
- Cooper TAL06P-C1
- Cooper TAL06P-C2
- Leviton 6674
- Leviton DSM10
- Lutron C.L. Family - Gen. 2.0 or above
- Lutron MACL-153M
- Lutron NTCL-250
- Lutron PD-6WCL



S9382

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9382	045923093821	120	6.5	50W	0.96	MR16	GU10

  

Lamp Code	Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
6.5MR16/LED/40'/27K/120V/GU10	Dimmable	2-3/16"	2.00"	500	25000	2700	Warm White

  

CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty
80	40	48/12	Box	Yes	Yes	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

