



Cat# 71422
LED MINI Wall-PACK



Model :		71422
OVERALL LAMP PARAMETERS	Input Voltage	120 VAC (With Pre-Installed Photocell)
	Input Current	0.50A Max.@120V
	Input Power	22W
	Power Factor	PF≥0.95
	Luminance	1400LM
	Luminous Efficiency	65 LM/W
	CRI	>70
	Beam Angle	180°
	Main Structure	Aluminium + Polycarbonate
	Surface	Baking Varnish
LED DRIVER	Output Voltage	18.2-36 VDC
	Output Current	.9A
	Driver Efficiency	88%
LED	LED Type	XBD
	LED Quantity	14 PCS
	LED Manufacturer	Cree
	LED Efficacy	110 lm/W
	Color Temperature	WW/NW/CW/R/G/B 5000K
LIFESPAN & ENVIRONMENT	Lifespan	50000 Hrs.
	Warranty	5 Years
	IP Rating	IP54
	Operating Temperature	-40F to 131F
	Storage Temperature.Humidity	-40°C—+80°C , 10—90% RH
SAFETY&EMC	Safety Norms	EN60598, EN61347-2-13, EN62031, EN62471, UL1598, UL8750
	Withstand Voltage	I/P-FG: 2121VDC
	Grounding Resistance	25A 100mΩ
	Electromagnetic Compatibility	EN55015, EN61000-2-3, EN61000-3-3, EN61547
OTHERS	Diamension	Pls refer to attached diamension drawing
	Net Weight(Kg)	4.3
	Gross Weight(Kg)	5.2
	Box Size	--
	Carton Size	390*230*315
	Q'ty / Carton	1

Dimensions: 71420

