



[Log in](#) | [Register](#)

Switch to   

search



[Products ▼](#) [Market ▼](#) [Solutions ▼](#) [Resources ▼](#) [About Us ▼](#) [Presentations](#)

Start --> Search=C11JA* --> C-11JA



C-11JA

Cast Bronze Clamp, Armored Cable to Water Pipe, 10
AWG - 6 AWG, 1/2" - 1" Water Pipe

Image | Line Art | 3D Model | Video | Customer
Drawing

Email Datasheet

[Print Datasheet](#)

Add to Favorites

Specifications Documents

Dimensional	General	Conductor(s)	Physical	Approvals / Certifications	Other Features
-------------	---------	--------------	----------	----------------------------	----------------

Dimensional	
Pipe Size (Range)	3/8 in-1 in
General	
Product Description	Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 6 AWG, 1/2 " - 1 " Water Pipe
Conductor(s)	
Copper Solid Size (Range)	10 AWG-6 AWG
Copper Stranded (Range)	8 AWG-6 AWG
Physical	
Type of Hardware	Steel - Zinc Plated
Type of Plating	Unplated
Ground Strap	N
Plated (Yes or No)	N

For Armored Cable	Y
Product Material	Bronze Alloy
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
Rated for Direct Burial	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467
Other Features	
UPC	7818101421100

© BURNDY® LLC 2011-2013 | [Distributors](#) | [Sales](#) | [Terms of Use](#) | [Site Map](#)

