



# S9393

45W/LED/HID/5000K/100-277V/EX39  
45 watt - LED HID Replacement; 5000K; Mogul extended base;  
100-277 volts

## Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- DLC approved
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C

## Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Minimum lamp compartment dimensions:

235mm x 235mm x 440mm (9.25" x 9.25" x 17.3")

Optional accessory: In-line surge protector [80-929](#)



S9393

| Item Number | Product Line | UPC          | Input Voltage | Watts | Incandescent Equivalent | Fluorescent Equivalent | HID Equivalent |
|-------------|--------------|--------------|---------------|-------|-------------------------|------------------------|----------------|
| S9393       | Hi-Pro       | 045923093937 | 100 - 277     | 45    | 300W                    | 65W                    | 175W           |

| Base           | ANSI Base | Lamp Code                       | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
|----------------|-----------|---------------------------------|-----------------------|--------|---------------|---------------|----------------|
| Mogul Extended | EX39      | 45W/LED/HID/5000K/100-277V/EX39 | Non-Dimmable          | White  | 10-3/4"       | 3.69"         | 5400           |

| Average Rated Hours | Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | DLC ID: |
|---------------------|-------------|-------|-----|-----------------|------|--------------|---------|
|---------------------|-------------|-------|-----|-----------------|------|--------------|---------|

|                |      |                  |     |                             |    |                                |                                        |
|----------------|------|------------------|-----|-----------------------------|----|--------------------------------|----------------------------------------|
| 50000          | 5000 | Natural Light    | 80+ | 300                         | 12 | Box                            | PAMXSTF9<br><a href="#">DLC Search</a> |
| RoHS Compliant |      | UL or ETL Listed |     | UL Classification           |    | Warranty                       |                                        |
| Yes            |      | Yes              |     | cULus - Damp Location Rated |    | <a href="#">5 Year Limited</a> |                                        |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051