



Powering Business Worldwide

pe.eaton.com

Type CH 3/4-inch Ground Fault Circuit Breaker

CH250GF

UPC:782113912899

Dimensions:

- **Height:** 2 IN
- **Length:** 6 IN
- **Width:** 2 IN

Weight: .8 LB

Notes: Two-Pole 120/240V Common Trip Requires Two 3/4-Inch Spaces

Warranties:

Specifications:

- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Used With:** Type CH Loadcenters
- **Main Circuit Breaker:** CH
- **Trip Type:** Common
- **Wire Size:** #14-6 AWG Cu/Al 60°C or 75°C

Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Drawing Dataset](#)
- [Eaton Specification Sheet - CH250GF](#)

Certifications:

- UL 489

Product compliance: No Data

