

763F








Finish Pack: 50 CFM 2.5 Sones Fan/Light with Transparent Polymeric Lens and Resin Grille; 100-watt Incandescent Lighting



Write the first review

Product Q&A 1 question | 1 answer
Read all Q&A



-  [Spec Sheet](#)
-  [Tools & Resources](#)
-  [Installation Guide](#)
-  [Where to Buy](#)
-  [Product Catalogs](#)
-  [Shop for Parts](#)
-  [Print](#)

Overview	Video Links	Specifications	Reviews	Answers
----------	-------------	----------------	---------	---------

Bathrooms up to (X) Square Feet	45
Ceiling Installation	Yes
CFM @ 0.10"	50
CFM @ 0.25"	39
Color	White
CSA	Yes
cUL Listed	Yes
Duct Direction	Horizontal
Duct Size	4"
ENERGY STAR® certified product	No
Grille Finish	White Polymeric
Grille Length	10-3/4"
Grille Width	12"
Housing Dimension LxWxH	8-1/4" x 8" x 5-3/4"
Humidity Sensing	No
HVI Certified	Yes
Light Bulb Quantity	1
Light Bulb Wattage	100
Light Bulbs Included	No
Lighting Type	Incandescent
Minimum construction space required	2" x 6"
Motion Sensing	No
Motor engineered for continuous operation	No
Nightlight	No
Product Weight (Pounds)	6.0
Project Pack	Yes
Rated Amps	1.6
Rated Sones	2.5
UL Listed for use over bathtubs or showers when connected to a GFCI circuit	Yes
Wall Installation	No
Warranty	1 Year
Watts @ 0.1"	42.1
Watts @ 0.1" (Max CFM)	42.1