



S3810

40A15/CL
40 watt A15 Incandescent; Clear; 2500 average rated hours;
290 lumens; Medium base; 130 volts

Features

- General Service Incandescent
- Household or Commercial use
- Long Life
- 130 volt



S3810

Item Number		UPC		Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3810		045923038105		40	A15	Medium	E26	40A15/CL	130
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours		Pack	Package Type	
Clear	3-1/2"	1.88"	C-9	290	2500		500/25	Box	
Dimmable/Non-Dimmable					RoHS Compliant				
Dimmable					Yes				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

