



Candle LED

4.5BA12/LED/827-22/E12/DIM 120V

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data


General Information		Starting Time (Nom)	
Cap-Base	E12 [Candelabra Screw]		0.5 s
Bulb Shape	BA12	Warm Up Time To 60% Light (Nom)	instant full light
Nominal Lifetime (Nom)	25000 h	Power Factor (Nom)	0.7
Switching Cycle	50000X	Voltage (Nom)	120 V
Technical Type	4.5-40W		
Light Technical		Temperature	
Color Code	822-827 [tunable warm white]	T-Case Maximum (Nom)	100 °C
Luminous Flux (Nom)	330 lm		
Luminous Flux (Rated) (Nom)	330 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2200-2700 K	Mechanical and Housing	
Color Consistency	ANSI 2700K	Bulb Finish	Clear
Color Rendering Index (Nom)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Suitable For Accent Lighting	No
		Energy Efficiency Label (EEL)	Not applicable
		Energy Consumption kWh/1000 h	4.5 kWh
Operating and Electrical		Product Data	
Input Frequency	60 Hz	Order product name	4.5BA12/LED/827-22/E12/DIM 120V
Power (Rated) (Nom)	4.5 W	EAN/UPC - Product	046677457211
Lamp Current (Nom)	45 mA		
Wattage Equivalent	40 W		

Candle LED

Order code	929001167104
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001167104

Net Weight (Piece)	0.063 kg
--------------------	----------

Dimensional drawing



LED 4.5-40W E12 BA12 CL DIM

Product	D	C
4.5BA12/LED/827-22/E12/DIM 120V	38 mm	125 mm

