



# Catamount®

## Heavy-Duty

### T&B Catalog Number:

L-24-120-0-L

### UPC Number:

72849491276

### Status:

Active

### Description:

Heavy Duty Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 599.72mm (23.611 Inches), Width of 7.62mm (0.30 Inches), Thickness of 1.91mm (0.075 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

### General

Material	Nylon 6.6 Weather Resistant
Color	Black

### Dimension Information

Nominal Length (inches)	24
Length (inches)	24.2
Width (inches)	0.300
Max. Wire Bundle Diameter (inches)	7
Min. Wire Bundle Diameter (inches)	3/16

### Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

### Tooling

Application Tools	ERG120
-------------------	--------

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.44 lbs. per 100

### Application Support

Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.

T&B Technical Support  
MS 3B-50

Hours: 7AM - 6PM CDT  
Monday-Friday

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)