



# Ocal®

**Channel-PVC Coated**  
**T&B Catalog Number:**

**UPC Number:**

**Status:**

**Description:**

A12P-G

70450843854

Active

PVC Coated Standard Punched Channel Strut, 1-5/8 Inch Depth, 12 Gauge, 10 Foot Long, Steel, Gray

## Features

Channels cold formed from hot-rolled pickled and oiled strip steel

## General

Material	Steel
Finish	PVC Coated
Color	Gray

## Dimension Information

Length (feet)	10
Material Thickness (ga.)	12

## Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

## Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

## Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	500
T&B Sold in UOM	Feet
T&B Weight Per UOM	2.01 lbs. Each

## Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

## Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)