



Hoffman

Hinge-Cover, Small, Type 3R

Catalog Number: A10R86HCR
US List Price (USD): \$84.09

Bulletin Number:

- A3SM

Material:

- Steel



Model Code:

- 38740

Ship Wt. Std. Pkg. (lbs):

- 25.5

Interchangeable:

- False

Industry Standards:

UL 50, 50E Listed; Type 3R; File No. E27567 cUL Listed per CSA C22.2 No 94;
Type 3R File No. E27567 NEMA/EEMAC Type 3R IEC 60529, IP32

Description

These enclosures have a size range of 6 x 4 x 4-in. to 12 x 12 x 10-in. and meet basic functionality requirements for applications that require protection from rain, sleet, snow or dripping water.

Applications:

These enclosures have a size range of 6 x 4 x 4-in. to 12 x 12 x 10-in. and meet basic functionality requirements for applications that require protection from rain, sleet, snow or dripping water.

Features:

- Drip-shield top and seam-free sides, front and back
- Plated steel hinge has stainless steel pin
- Weldnuts provided for mounting optional panels
- Provisions for padlocking on zinc-plated draw-pull catch
- Knockouts on bottom of enclosure
- No gasketing

Specifications:

16 gauge galvanized steel

Finish:

ANSI 61 gray polyester powder paint finish inside and out over galvanized steel. Optional solid panels are white and optional perforated panels are gray.

Accessories:

- Industrial Corrosion Inhibitors
- Grounding Device
- Panels for Type 1 Enclosures and Small Type 3R Enclosures
- Touch-Up Paint

Notes:

- Purchase panels separately.
- Purchase perforated panels separately.

Technical Data

Hinge-Cover, Small, Type 3R

Catalog Number	A10R86HCR
A in.	10
B in.	8
C in.	6
Panel	A10N8P
Perforated Panel	A10N8PP
Panel Size D x E in.	8.25 x 6.25
Mounting G in.	11.00
Overall L x W in.	12.00 x 8.81
Knockout Pattern	F-G-H-I

Certifications



UL Certification

Documents



Spec Sheet



Instruction Manual



Instruction Manual



Dimension Drawing

No accessories available.