



Representative Image

## Catalog No. CR353FF3BH1

### Description:

### UPC No

### Home > Contactors > Definite Purpose Controls > Definite purpose contactor

Contactors, Definite Purpose, Non-Reversing, Amp Rating: Full Load 60, Locked Rotor 300 @ 480 VAC, Maximum Voltage: 600 VAC, Coil Voltage: 24 VAC @ 50/60 Hz, Enclosure Type: Open, Dimensions: 2.74 Inch W x 3.58 Inch D x 3.75 Inch H, Features: Universal Mounting Plate CR353FF3

### Descriptors

|             |                            |
|-------------|----------------------------|
| Category    | Definite purpose contactor |
| GO Schedule | 10DP                       |

### Specifications

|       |   |
|-------|---|
| Poles | 3 |
|-------|---|

## Publications

| Title                                                                                                      | Publication No. | Publication Type                 |
|------------------------------------------------------------------------------------------------------------|-----------------|----------------------------------|
| <a href="#">353F 25-150A DP Cont w/250V Aux Open</a><br>GEP1260-04-005353F 25-150A DP Cont w/250V Aux Open | GEP1260-04-005  | Drawings-Outline and Dimensional |

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.