



Catamount®

Mounting Head

T&B Catalog Number:

UPC Number:

L-11-50MH-0-C

Status:

72849491060

Description:

Active

Cable Tie 50lb 11" Ultraviolet Resistant Black All-Nylon #10 Mounting Hole 100 Per Bag

General

Material	Nylon 6.6 Weather Resistant
Color	Black
Mounting Hole Size	#10

Dimension Information

Nominal Length (inches)	11
Length (inches)	11.1
Width (inches)	0.187
Max. Wire Bundle Diameter (inches)	3
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, ERG120, QC-100, L-200, L-400-C
-------------------	---------------------------------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	5.48 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000303
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com