



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Series Non-Reversing Reset Overload Relay Starter

AN16DN0AB

UPC: 782113971704

Dimensions: 4.61 IN * 4.38 IN * 3.31 IN (L * W * H)

Notes: Heater Packs must be purchased separately

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Starter w/C306 bi-metal OLR
- **Amperage Rating:** 27A
- **Max Hp Rating:** 2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V
- **Mounting:** Horizontal
- **Number Of Poles:** Three-pole
- **Phase:** Single-phase, three-phase
- **Size:** 1

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [AN16DN0_B AutoCAD 2D Footprint](#)
- [AN16DN0_B 2D Drawing Xchange](#)
- [AN16DN0_B 3D Inventor](#)
- [AN16DN0_B AutoCAD 2D Footprint \(mm\)](#)
- [AN16DN0_B 2D PDF](#)
- [AN16DN0_B 3D Model Xchange](#)
- [Quick Selector - NEMA Contactors](#)

Certifications: No Data

Product compliance: No Data



