



GE
Lighting

32273 - GE LED Bright Stik™

LED10LS3/850

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Dimmable	No
Primary Application	General Purpose
Product Color	White
Rated Life (Hours)	15000 h
Base	E26
Bulb Shape	A19

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	76
Initial Lumens-nominal	760 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	32273
Description	LED10LS3/850

DIMENSIONS

Bulb Max Overall Length-MOL	4.45 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	10 W