



## 4933291S-15: LED Wall Sconce



### Dimensions:

**Width:** 11 3/4"

**Height:** 8 3/4"

**Weight:** 2.7 lbs.

**Extends:** 4"

**Wire:** 6 1/2"

**Mounting Proc.:** Wall / Bath

**Connection:** Mounted To Box

**Bulb Type:** Modules

**Bulb Base:** Integrated

**Volts:** 120

**Watts:** 14

**Watts Consumed:** 14

**Watts Rated:** 14

**Hours Rated:** 50000

**Lumens:** 1000

**Bulb Temp:** 2700 °K

**CRI:** 90

**Collection:** ADA Wall Sconces

**UPC #:** 785652278297

**Finish:** White (15)

### Features:

- Meets American with Disabilities Act standard extension requirements
- Advanced LED technology that warms in color when dimmed (2700K - 2200K).

### Material List:

1 Body - Steel - Undefined

### Safety Listing:

Safety Listed for Damp Locations

### Instruction Sheets:

Trilingual (English, Spanish, and French) (990W4933291S-ADA)

Trilingual (English, Spanish, and French) (990W49332BLE-ADA)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Acrylic	Undefined	1			11 3/4	8 3/4					

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	8	9 19/32	1 1/2		4 1/2	

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	4933291S-15	1	785652278297	14	11.25	6	0.547	3.5	125	Yes
Master Pack	4933291S-15	4	10785652278294							
Shipping Master	4933291S-15	4	20785652278291	24.5	14.5	12.25	2.518	16.1	125	Yes

NJ Pallet		120		48	40	73	81.111	483		No
NV Pallet		120		48	40	78	86.667	478.5		No