



Catalog#: OD80
80CFM DELUXE VENTILATION FAN

Category FANS
Page [J5](#)
Barcode 8-35243-10762-5

Features:

Housing:

- Dimensions: 9-1/8" L x 9-1/8" W x 7-5/8" H [[ODH](#)]
- Heavy-duty steel housing coated with rust proof paint
- Adjustable double bar hanger system that extends up to 24"
- 4" exhaust pipe connection
- Wired for fan
- Effortless side electrical connection
- Termination damper to prevent cold air infiltration [45LT-D]
- Light, durable, and sturdy

Motor and Blower:

- Power rating of 120V / 60Hz
- Permanently lubricated, energy efficient motor with **ball bearings** designed for continuous use
- Quick installation of motor and impeller assembly
- Effortless snap in wiring connection
- UL and cUL listed for tub/shower enclosure when connected to a GFCI protected branch circuit

Grille: [[OD-G](#)]

- Contemporary design - with or without light kit
- Electronic ballast
- Durable white ABS for easy cleaning
- Torsion spring clips included for easy mounting

Packaging Info:

Master Qty. 4
 Weight 10 lbs

Warranty 2 year limited warranty

Document [Installation Instruction](#)

Certifications



TITLE 24 COMPLIANT 

Catalog Number	Air Volume	Static Pressure	Noise	Power Consumption	Speed	Current	Power Rating	Energy Efficiency	Duct Diameter	Motor
OD80	80 CFM	0.1" w.g.	0.8 sone	27.9 W	946 RPM	0.18 Amps	120V / 60Hz	2.87 CFM/W	4"	Enclosed

