

Jolie Collection
Jolie 3 Light Bath Light NI
45639NI (Brushed Nickel)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Dimensions

Height	9.25"
Width	20.25"

Ordering Information

Product ID	45639NI
Finish	Brushed Nickel
Available Finishes	CH, CH, NI, NI, OZ, OZ
Collection	Jolie Collection

Dimensions

Extension	8.00"
Height from center of Wall opening	4.75"
Base Backplate	8.75 X 4.50
Weight	4.30 LBS

Specifications

Material	Steel
Diffuser Description	Satin Etched

Electrical

Voltage	120 V
---------	-------

Qualifications

Safety Rated	Damp
Warranty	www.kichler.com/warranty

Installation

Install Glass Up or Down	Yes
--------------------------	-----

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	3
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	23-30W		