



LED18WT8F/48/840K-G6D



Description	4000K GLASS BALLAST BYPASS DLV V3.1 4FT 18W-1800LM 2BD NON-DIM 80 CRI 120-277V
Ordering Code	09010
UNSPSC Code	39112102

Specifications

Voltage Rating	120~277
Voltage Type	AC
Watts	18
Amps	0.15
Lumens per Watt	100
Base Type	G13
Bulb Type	T-8
MOL in/mm	48.0/1219
Length	4'
MOD in/mm	1.1/28
Lumens	1800
CT deg K	4000
CRI	80+
Beam Angle	196°
Rated Life	55,000
Ambient Operating Temp Range	-40° C (-40° F) to 40° C (104° F)

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 • (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 • (P) 1.888.410.8151 (F) 1.888.705.1335