



Measurements:

<u>Height</u>	<u>Width</u>
4.50"	7.50"
<u>Max OAH</u>	
4.50"	
<u>Hanging Weight</u>	
1.54 lb	

Lamping:

Incandescent MB Incandescent	672 Rated Lumens
1.00 60W MB Incandescent	Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
2.10 lb	9.45"	6.50"	9.45"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
20.62 lb	10.40"	20.50"	28.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
8.0000	783209112841	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location  
Location

Additional:

MB Incandescent (Not Included)