



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
4.75"	24.00"	2.30"
<u>BP Height</u>	<u>BP Width</u>	
24.00"	4.75"	
<u>Hanging Weight</u>		
2.12 lb		

Lamping:

Incandescent MB Incandescent	4,600 Rated Lumens
4.00 100W MB Incandescent	Color Temperature
400 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
2.52 lb	5.12"	2.56"	24.61"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
20.13 lb	10.63"	10.63"	25.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
8.0000	783209712423	Yes	

Finish:

Polished Chrome PC

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB Incandescent (Not Included)
Lighting Direction: Both