PLS 5.5W BYP 2GX7 TITANIUM LED SERIES











- Built-in universal voltage driver Bypass installation
- (1) 180° rotatable base
- Exceptional efficacy 91 LPW
- Last 4 times longer than CFL
- Compact form factor fits most fixtures
- Suitable for use in totally enclosed fixtures































PLS 5.5W BYP 2GX7 TITANIUM LED SERIES









Base: 2GX7 (4-pin CFL)

Voltage: 120-277V

Dimmable: No PF: 0.9

Lifetime: 50,000 hrs Weight: 0.06lb. / 26g



SPECIFICATIONS

Model	Product	Power (W)	сст	CRI (typ.)	Lumens	LPW	Beam Angle
5.5PLS/835/BYP/2GX7	57826	5.5	Neutral White 3500K	80	500	91	120°

^{*} Suitable for use in totally enclosed fixture

^{**} Suitable for damp locations. Not for use where directly exposed to weather or water

^{***} Full installation guide and more details available on website