

# Model: EN-24100-277-RB2-T

## Electronic Transformer

# WAC LIGHTING

Responsible Lighting®



Fixture Type:

Catalog Number:

Project:

Location:

### PRODUCT DESCRIPTION

Low voltage electronic transformer designed to be used as an enclosed remote transformer. Enclosure has separate compartments for transformer, line and low voltage wiring. Transformer may be safely loaded to 100% of stated capacity.

### FEATURES

- U.L.2108 listed electronic low voltage transformer
- Built-in auto reset, soft start, short and overload circuit protection features. Soft start delayed start feature extends lamp life.
- In the case of a system overload or short circuit the transformer will revert to a "hold" position and then automatically reset the system when the problem is solved. System protection is designed to last several hours.
- 1W minimum load; 96 maximum load
- 6' InvisiLED 24V lead wire preinstalled. Separately included is 6' lead for Straight Edge and Line and Line 2.0 applications.

### SPECIFICATIONS

**Input:** 100-240VAC (50/60Hz), 277VAC (50/60Hz)  
**Output:** 24V DC (20khz)  
**Standards:** UL & CUL Listed

### ORDER NUMBER

Model	L	W	H
EN-24100-277-RB2-T	12 <sup>5</sup> / <sub>8</sub> "	3 <sup>1</sup> / <sub>4</sub> "	1 <sup>7</sup> / <sub>8</sub> "

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585