



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5899-108

Penfield

Smooth contemporary curves highlighted by a clear glass exterior surrounding an opal glass interior. Aluminum and brass construction. Two-light wall lantern .

Category: Outdoor

Finish: Oil Rubbed Bronze (painted)

Construction: Die-cast aluminum construction

Glass: Outer clear glass cylinder, Inner white opal glass cylinder



Width: 8"
Height: 24"
Depth: 10-3/8"
H/CTR: 12-1/4"

Glass: Outer 6-1/4" dia., Inner 5" dia.
 Height: Outer 22-1/4" , 22-5/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box 5", 23-3/8"ht., 1"depth	Pre-wired 6" of wire supplied 120V	Quantity: 2 100W Medium Base Medium porcelain sockets	cCSAus Wet location listed 1 year warranty Companion fixtures are available