

F3019/3SN: 3 - Light Island



Dimensions:

Width:	36"	Overall Height:	58 3/4"
Height:	14 1/8"	Extends:	9 1/2"
		Wire:	180" (color/Black/White)
		Connection:	Mounted To Box

Bulbs:

3 - Medium A19 75w Max. 120v - Not included

Features:

•

Material List:

- 1 Body - Steel - Satin Nickel
- 1 6" Stem - Steel - Satin Nickel
- 3 12" Stem - Steel - Satin Nickel

Safety Listing:

Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (F3017-3_F3019-3_F3021-3)

Collection: Hobson

UPC #: 014817527209

Finish: Satin Nickel (SN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Clear Seeded	3									

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	F3019/3SN	1	014817527209	39.25	15.5	12.75	4.489	17.6	250	Yes
NJ Pallet		15		48	40	68.5	76.111	264		No
NV Pallet		15		48	40	68.5	76.111	264		No