

Cahoon Collection
Cahoon 3 Light Linear Chandelier in AVI
43774AVI (Anvil Iron)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Dimensions

Height	13.00"
Overall Height	51.00"
Length	37.25"
Width	13.50"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	23-30W		

Ordering Information

Product ID	43774AVI
Finish	Anvil Iron
Collection	Cahoon Collection

Dimensions

Base Backplate	16.25 X 4.75
Chain/Stem Length	36.00"
Weight	35.20 LBS

Specifications

Material	Steel
Glass Description	Etched Tempered
Shade Description	Biege Linen

Electrical

Voltage	120V
Lead Wire Length	111.00"

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	3
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19