



Job Name:		Item Number:	
Specifier Name:		Sales Agency:	
Specifier Contact:		Agency Contact:	
Fixture Type:		Comments:	
Quantity:		Approval:	

75W 12V Hardwire Transformer



Description

Ambiance magnetic transformers are encased in a metal, black powder coated enclosure and potted to minimize noise and vibration. They are listed, thermally protected, and dimmable along with having resettable circuit breakers for short circuit protection. Housings feature an easy-hang bracket, wiring access door and multiple convenience knockouts for line voltage entry. Boost tap included for when transformer is located 20 feet or more from lighting system.

Specifications

Item Number	94458-12
Finish	Black
Dimensions	L: 8 3/4" W: 4 1/4" H: 3 3/4"
Mounting Proc.	Screw(s)
Safety Listing	UL Listed for Dry Locations cUL Listed for Dry Locations
Warranty	1-Year Warranty

Instruction Sheets

- Trilingual (English, Spanish, and French)
(990RM07512)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	94458-12	1	785652116506	12	7.25	6.25	0.315	7.8	Yes
Master Pack	94458-12	4	10785652116503	15.75	13.25	13.25	1.6	32.6	Yes