

MINKA-LAVERY®

Item #: **3383-77**
 Product Family Name: **D'or**
 Category: **Bath**
 Certification: **3057374**
 Patents
 Notes:

UPC Code: **747396098272**
 Finish: **Chrome**
 Category Type: **Bath**



Image File Name:
 3383-77--
 1475636406.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
23.13		7.75	7.75
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	9.59
Canopy Width:	Canopy Height:	Canopy Length:	
8.50	4.75		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		3.75	4.00

LAMPING

No. of Bulbs:	Light Type:			
3	A-19,Medium			
Max Bulb Wattage:	Socket:			
100	E26,Medium			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes			N	No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Carton Width:	Carton Height:	Carton Length:
10.250	12.000	25.630
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
12.740	1.824	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1

SHADE / GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
G3381	3
Width:	Height:
5.25	5.75
	Length:
	5.25



Damp
 Location
 Yes



ETL Intertek
 Yes