



# S9630

6.5R20/LED/2700K/525L/120V  
6.5watt; LED R20; 2700K; 107° beam spread; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable

### Compatible Dimmers

- Leviton VPE04
- Lutron C.L. Family - Gen. 2.2 or above
- Lutron PD-6WCL
- Lutron SELV-300P



S9630

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9630	DiTTO	045923096303	120	6.5	50W	0.90	R20
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	6.5R20/LED/2700K/525L/120V	Dimmable	Frosted	3-15/16"	2.50"	525
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR
25000	2700	Warm White	80	107	24/6	Box	ENERGY STAR
RoHS Compliant	UL or ETL Listed	UL Classification	Warranty				
Yes	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>				



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

