



On Line Catalog



BURNDY Catalog Number	KSA4
UPC Number	7818100154077
Description	TRITAP SERVIT 4STR-10SOL
Status	Active

Web Use
BURNDY Product Line

	Dimensional
Width (in)	0.62
Height (in)	0.71
Size (Hex) or Size (Bolt)	5/8
Cross Flats	0.81
Size (Hex) or Size (Bolt) - in	0.63
B Length (in)	1.10
Bolt Diameter (in)	0.62
Min Tap Size with Max Run Size	#4 Str. (.232) - #10 Sol. (.102)
Max Tap size with Max Run Size	#4 Str. (.232) - #4 Str. (.232)
Min Tap Size with Min Run Size	#8 Sol. (.129) - #10 Sol. (.102)
B Length (Fraction)	1-1/9

	General
Product Description	Aluminum Split Bolt, (Run,Tap):: Al-Al: 4 AWG (Str), 4 AWG (Str) , Al-Cu: 8 AWG (Sol), 10 AWG (Sol) , Cu-Cu: 4 AWG (Str), 10 AWG (Sol), Tin Plated

	Conductor(s)
Aluminum Run Size (Range)	8 AWG-4 AWG
Copper Tap Range	10 AWG-4 AWG
Copper Stranded Run (Range)	8 AWG-4 AWG
Copper Solid Tap (Range)	10 AWG-4 AWG
Aluminum Tap Size (Range)	8 AWG-4 AWG

	Physical
Installation Torque	165
Type of Plating	Tin
Plated (Yes or No)	Y
Product Material	Aluminum

	Approvals / Certifications
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Services

Hours: 8:00 AM - 5:00 PM
Monday - Friday

