



Item #:	UPC Code:
F787-ORB	706411054426
Product Family Name:	Finish:
Simple	Oil Rubbed Bronze
Category:	Category Type:
Exterior Fan	Ceiling Fan
Certification	
4009339	
Patents	
Notes:	



Shown with Optional
Light Kit #: K9787L-ORB (Not Incl.)

Image File Name:
F787-ORB--
1456822923.jpg



MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
ABS		No	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	3	14 DEGREES	10.80
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
3.5		6.	
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
10.00	9.50	8"	123X30MM

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	51	80.00	109	138.00	191
Amps:	0.05	0.08	0.13	0.20	0.43
Watts:	2.980	5.40	9.100	14.30	33.100
CFM:	2032.00	3084.00	4108.00	5224.00	7051.00
CFM/Watts	681.88	571.11	451.43	365.31	213.02



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	No
	Included Remote Control:	Included Wall Control:
	RC400	
	Compatible Remote Control[s]:	Compatible Wall Control[s]:

LAMPING

No. of Bulbs:	Light Type:			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:
8.630	9.000	26.750
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
12.540	1.202	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack:
		1



Wet Location

Yes



ETL Intertek

Yes