



## 53059-15: Two Light Ceiling Flush Mount



### Dimensions:

<b>Diameter:</b>	9 1/2"	<b>Wire:</b>	6 1/2"
<b>Height:</b>	4 3/4"	<b>Mounting Proc.:</b>	Key Slots
		<b>Connection:</b>	Mounted To Box

### Bulbs:

2 - Medium A19 60w Max. 120v - Not included

### Features:

- Sleek architectural look with exclusive 'twist-lock' design makes installation and relamping easy with no exposed screws

### Material List:

1 Body - Steel - White

### Safety Listing:

Safety Listed for Damp Locations  
Safety Listed for Damp Locations

### Instruction Sheets:

English (HC-677)  
French (F-001)

**Collection:** Twist-Lock Fitters

Two Light Close to Ceiling in White Finish with Satin White Glass.

Ref.#: 5359.

**UPC #:**785652530593

**Finish:** White (15)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Satin White	1				4 5/16	9 1/2				

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	53059-15	1	785652530593	10.75	11	7.25	0.496	4.15	100	Yes
Master Pack		6	10785652530590	22.25	11.5	23.75	3.517	26.45	100	Yes
NJ Pallet		84		48	40	72	80	370.3		No
NV Pallet		108		48	40	72	80	476.1		No