



Carlon®

ENT Flexible Raceway

T&B Catalog Number:

12007R-100

UPC Number:

03448123193

Status:

Active

Description:

3/4 inch. Flex-Plus ENT non-metallic red flexible raceway, 100 foot.

Features

Recognized for use with PVC rigid non-metallic conduit fittings with all size of ENT.

One piece ENT coupling, threaded terminator and rigid non-metallic conduit fittings are rated concrete tight without tape.

Lightweight, hand bendable, and free from sharp edges which reduces installation time and saves money.

Application

Flex-Plus Blue ENT is a non-metallic flexible raceway for use in walls, floors, and non-plenum ceilings.

Residential, low or high rise, multi or single family. Commercial applications - low or high rise - office, retail, hotel/motel and restaurants.

Other applications include schools, classrooms, dormitories, offices, fire alarm systems, solar photovoltaic systems, recreational vehicles and parks, and marinas and boatyards.

General

Pull Tape	Empty
Material	Non-Metallic
Color	Red
Component Type	Flexible Raceway

Dimension Information

Size (inches)	3/4
Nominal Inside Diameter (inches)	0.76
Nominal Outside Diameter (inches)	1.05
Coil Length (feet)	100
Minimum Bend Radius (inches)	6

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	12.88 lbs. per 100

Application Support

Product Specifications-Flex-Plus Blue ENT	Available on Website
Application Handbook-ENT	Available on Website

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 73317

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com