



Liquid Tight Connectors Reusable Fittings

- Industrial specification grade steel, zinc plated
- Malleable iron body
- UL rated Liquid Tight
- Includes sealing washer
- Bonds conduit to box or enclosure
- Corrosion resistant protection from moisture & oils
- Designed to protect against excessive vibration

90° Angle Connectors

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
STR3890**	3/8"	10	100	24
STR5090**	1/2"	10	100	24
STR7590**	3/4"	5	50	38
STR10090**	1"	5	25	70
STR12590**	1-1/4"	2	20	88
STR15090**	1-1/2"	1	10	125
STR20090**	2"	1	5	180
STR25090	2-1/2"	-	2	625
STR30090	3"	-	1	900
STR35090	3-1/2"	-	1	1000
STR40090	4"	-	2	1500

** Steel Nut

Dimensional Table

Cat. #	A	B	C Length of Thread
STR3890/B	1.25	1.59	.59
STR5090/B	1.25	1.66	.59
STR7590/B	1.53	1.78	.59
STR10090/B	1.84	2.19	.66
STR12590/B	1.94	2.38	.69
STR15090/B	2.09	2.63	.72
STR20090/B	2.41	3.06	.72
STR25090/B	8.00	9.25	1.50
STR30090/B	8.75	10.50	1.50
STR35090/B	10.93	11.50	1.50
STR40090/B	12.63	13.00	1.50

UL rated suitable for hazardous locations

Class I, Div. 2; Class II, Div. 1 and 2;

Class III, Div 1 and 2; NEC 501-4(b), 502-4(a) (2), 503-3(a)

90° Angle Connectors with Insulated Throat

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
STR3890B**	3/8"	10	100	24
STR5090B**	1/2"	10	100	24
STR7590B**	3/4"	5	50	38
STR10090B**	1"	5	25	70
STR12590B**	1-1/4"	2	20	88
STR15090B**	1-1/2"	1	10	125
STR20090B**	2"	1	5	180
STR25090B	2-1/2"	-	2	625
STR30090B	3"	-	1	900
STR35090B	3-1/2"	-	1	1000
STR40090B	4"	-	2	1500

** Steel Nut

