



75661-839: Two Light Ceiling Flush Mount



Collections: Winnetka (Primary)
Uptown

Medium Flush Fixture in Blacksmith Finish with Satin Etched Glass Shade

UPC #:785652756634

Finish: Blacksmith (839)

Dimensions:

Diameter: 14" **Wire:** 6 1/2"
Height: 5 1/4" **Mounting Proc.:** Key Slots
Weight: 4.6 lbs. **Connection:** Mounted To Box

Bulbs:

2 - Medium A19 60w Max. 120v - Not included
2 - LED Medium A19 8w Max. 120v - Not included
2 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Blacksmith

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

English (HC-1438)
French (F-001)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	1					11 13/16				

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	75661-839	1	785652756634	15.5	15.5	8.5	1.182	6.4	150	Yes
NJ Pallet		62		48	40	73	81.111	396.8		No
NV Pallet		62		48	40	73	81.111	396.8		No