



44662-839: Three Light Wall / Bath



Dimensions:

Width:	23"	Extends:	8 1/2"
Height:	9 1/4"	Wire:	6 1/2"
Weight:	9.3 lbs.	Mounting Proc.:	Wall / Bath
		Connection:	Mounted To Box

Bulbs:

3 - Medium A19 100w Max. 120v - Not included
3 - LED Medium A19 8w Max. 120v - Not included
3 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Fixture may be mounted in the up or down position
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Collection: Winnetka

Three Light Bath Bar in Blacksmith Finish with Satin Etched Glass Shades

UPC #:785652416644

Finish: Blacksmith (839)

Material List:

1 Body - Steel - Blacksmith

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

English (HC-1431)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	3				5 3/4	4	1 5/8			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	5 3/8	22 1/2	1 3/8		4	5 1/4

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	44662-839	1	785652416644	24.5	10	12.25	1.737	12	125	Yes
NJ Pallet		36		48	40	77	85.556	432		No
NV Pallet		36		48	40	77	85.556	432		No