



Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshow](#)s | [Support](#)

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Terminals, Kits and Tools](#) > [Terminals](#) > 3M™ Highland™ Vinyl Insulated Block Fork Terminal BFV14-10Q, AWG 16-14, 25/bag

[Find An Account Rep](#) [Where To Buy \(Find A Distributor\)](#) [Contact Us](#)

3M™ Highland™ Vinyl Insulated Block Fork Terminal BFV14-10Q, AWG 16-14, 25/bag

3M ID 80611602519 UPC# 00051128599907 Part Number **BFV14-10Q**

[Print](#)



3M™ Highland™ Color-Coded Block Fork is a lug connection terminal that ensures an ideal fit while offering reliable and safe performance. The terminal has a vinyl-insulated, butted-seam barrel and withstands temperatures of -40 to 221 degrees F (-40 to 105 degrees C). Electrolytic copper construction offers good conductivity and a tin-plated finish resists corrosion.

- Blue vinyl-insulated, butted-seam barrel ensures a secure fit and offers reliable performance
- Funnel-designed, polyvinyl chloride sleeve offers easy insertion of wires
- Suitable for use in a terminal block
- Stud size #10
- Accommodates wire sizes 16 to 14 AWG
- Electrolytic copper construction offers good conductivity
- Withstands a temperature range of -40 to 221 degrees F (-40 to 105 degrees C)
- 600V-rated for building wire and 1000V for signs, fixtures or luminaires
- UL Listed, CSA Certified and RoHS 2011/65/EU Compliant
- 25/bag

Need Help? [Contact Us](#)

Questions? We can help [Contact Us](#)

Overview

Documents

3M™ Highland™ Block Fork Terminal is color-coded for quick and easy identification of the wire size required. It has a butted-seam barrel that is covered by a funnel-designed, rigid-molded, polyvinyl chloride sleeve to guide the wire into position while providing electrical contacts and mechanical stress relief at the point of insulation. The abrasion-resistant, flared, vinyl-sleeve insulation ensures easy crimping. UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.

Specifications

Agency Approvals	UL and CSA
Barrel Length	0.25 Inch
Barrel Style	Butted
Brand	Highland
Clearance (C)	0.25 Inch
Conductor Size	16 - 14 AWG
CSA File Number	LR22190
Dimension E	0.7 Inch
Insulation Material	Vinyl
Length	0.85 Inch
Maximum Insulation Outer Diameter	0.17 Inch
Packaging	25 per bag
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Stud Size	10
Terminal Style	Block

Terminal Type	Fork
Thickness	0.03 Inch
Trademark	Highland
UL File Number	E23438
Width	0.3 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.