

HBL7810D -- Circuit-Lock Manual Motor Controllers & Disconnects



30A, 40A & 50A

#10 Brass terminal screw.

Clamping plate for secure back or side wiring.

Optional side guard.

For close wall applications and finger safe environments.

3 Pole, 30A 600V AC, Manual Motor Controller, Standard Toggle

Product Specifications

Product Type



Circuit-Lock Products

Circuit-Lock Item	AC Manual Motor Controllers
Circuit-Lock Amperage	30A
Circuit-Lock Poles	3 Pole
Circuit-Lock Voltage Rating	600V AC Max
Circuit-Lock Enclosure	None
Circuit-Lock Toggle Style	Standard
Circuit-Lock Wiring Style	Side Wired
Wiring Style	Back and Side Wired
Operating Temperatures	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Listing and Certifications	UL Listed and CSA Certified
Weight in LBs	0.55
UPC Number	783585202792

