



Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Terminals, Kits and Tools](#) > [Terminals](#) > 3M™ Highland™ Vinyl Insulated Ring Terminal RV14-10Q, AWG 16-14, 25/bag[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

3M™ Highland™ Vinyl Insulated Ring Terminal RV14-10Q, AWG 16-14, 25/bag

3M ID 80611602998 UPC# 00051128600382 Part Number RV14-10Q

[Print](#)

3M™ Highland™ Ring Tongue Terminal ensures an ideal fit while offering reliable and safe performance. The terminal has a vinyl-insulated, butted-seam barrel and withstands temperatures of -40 to 221 degrees F (-40 to 105 degrees C). Electrolytic copper construction offers good conductivity and a tin-plated finish resists corrosion.

- Blue vinyl-insulated, butted-seam barrel ensures a secure fit and offers reliable performance
- Funnel-designed, polyvinyl chloride sleeve offers easy insertion of wires
- Standard-style ring tongue fits around the stud
- Stud size #10
- Accommodates wire sizes 16 to 14 AWG
- Made of electrolytic copper for good conductivity and has tin plating for corrosion resistance
- Withstands a temperature range of -40 to 221 degrees F (-40 to 105 degrees C)
- 600V-rated for building wire and 1000V for signs, fixtures or luminaires
- UL Listed, CSA Certified and RoHS 2011/65/EU Compliant
- 25/bag

Need Help?

Questions? We can help
[Contact Us](#)



Overview

Documents

A ring is the standard style of tongue. The safest and most reliable; it cannot be removed unless mounting screw is removed.

Specifications

| | |
|--|--|
| Agency Approvals | UL and CSA |
| Barrel Length | 0.25 Inch |
| Barrel Style | Butted |
| Brand | Highland |
| Clearance (C) | 0.29 Inch |
| Conductor Size | 16 - 14 AWG |
| CSA File Number | LR22190 |
| Dimension E | 0.74 Inch |
| Insulation Material | Vinyl |
| Length | 0.9 Inch |
| Maximum Insulation Outer Diameter | 0.17 Inch |
| Packaging | 25 per bag |
| RoHS 2011/65/EU Compliant | Yes |
| RoHS EU Comments | RoHS 2011/65/EU compliant without exemption *Important RoHS information |
| Stud Size | 10 |
| Terminal Style | Standard |
| Terminal Type | Ring |

| | |
|-----------------------|-----------|
| Thickness | 0.03 Inch |
| Trademark | Highland |
| UL File Number | E23438 |
| Width | 0.33 Inch |

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.