



Actual

Catalog Number: L-7-50MH-9-M
Product ID: 7TAG054670R0011
UPC Number: 72849491690
EAN Number: 05414363154211
Status: Active

Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 205.70mm (8.1 Inches), Width of 4.6mm (0.18 Inches), Thickness of 1.35mm (0.053 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), #10 Screw for Mounting, Bulk Pack

- Application Tools: ERG50, ERG120, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Mounting Hole Cable Tie
Standard	UL E49405
Width	0.18 Inches/4.6mm
Length	8.1 Inches/205.70mm
Thickness	0.053 Inches/1.35mm
Bundle Diameter	0.0625 Inches/1.59mm-1.75 Inches/44.45mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Double Locking Head
Tensile Strength	50 Pounds/220 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.6mm
Length belt/tape/tie	205.7mm
Tie thickness	1.35mm
Min. holding force	220N
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	17x12x2
Outer Quantity	5000
Outer Dimensions (inches)	17x13.25x10.25
Weight Uom	3.76 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000303

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com