



CABLE PULLER ASSEMBLY,4000 LB (UT4)

4000 LB Cable Puller 120 VAC,60 HZ

Cat No: 52025854

UPC No: 783310215523

### Description

---

- Two pulling speeds to match the job
- Quick Latch system attaches to the outside of threaded and unthreaded conduit without the need for adapters
- Quick Set-Ups & Tear Downs- roll it to the job, adjust the boom and nose & attach it to the conduit
- Boom extends to 8'. A 12' boom extension accessory is available
- Integral foot operated on/off switch
- Nose can be turned for up, down & side pulls
- Rolls easily between job locations
- Available floor mount accessory for use in tight spaces
- Patented

## Specifications

---

- Accessory :
  - 10014 UPC 10014 Floor Mount For UT4 Cable Puller
  - 10015 UPC 10015 12.000 FT Long Extension Boom For Ut4 Cable Puller
  - 35283 UPC 35283 Double-Braided Composite Rope 9/16 IN X 300.000 FT (14.300 MM x 91.000 M)
  - 35284 UPC 35284 Double-Braided Composite Rope
  - Smaller detached nose & sheave fits in a wider range of applications
  - Remote control box includes LED lights which brightly display force in 500 lb. increments during pull
  - Foot pedal starts the motor without delay for increased productivity, removable for convenience
- Continuous Pulling Force : Low Speed 3000.000 LB (1364.000 KG)
- Drive Motor : 1-1/4 hp, 120 VAC, 60 Hz
- Electrical Plug : 120 V, 15 Amp
- Foot Switch : Standard
- Force Gauge : Standard
- High Pulling Speed : No Load: 26 FPM (8 MPM), 2000LB (909 KG) : 20 FPM (6 MPM)
- Low Pulling Speed : No Load: 13 FPM (4 MPM), 2000LB (909 KG) : 10 FPM (3 MPM)
- Maximum Pulling Force : High Speed 2000 LB, Low Speed 4000 LB
- Optional Long Boom Extension : 12.000 FT (3.600 M) Maximum
- Pulling Capability : 3 x 750 KMIL Cable 600.000 FT With 2 x 90° Bends, 4 x 350 KMIL Cable 400.000 FT With 4 x 90° Bends, 3 x 500 KMIL Cable 400.000 FT With 3 x 90° Bends
- Pulling Rope : 9/16 IN Diameter Double Braided Composite (16000 LB Minimum Breaking Strength)
- Standard Boom Extension : 8.000 FT (2.400 MR) Maximum
- Sub Brand : Ultra Tugger
- Weight : 175.000 LB (80.000 KG)