







# 60W 12V DC LED Driver

### 60W Voltage Dimmable Class 2 LED Driver

Product Code: E60L12DC-KO





Magnitude's E60L12DC-KO dimmable voltage LED driver is class 2 rated and designed to operate with any standard MLV/Incandescent TRIAC (Leading edge) dimmer switch. Encased in a low profile aluminum enclosure that includes 2 knock-outs to enable easy installation makes it the perfect choice for under cabinet lights, tape lights and various LED fixtures installations. Our electrical specification includes Auto Reset, over current and short circuit protection. Efficiency of 90% and higher allows the driver to operate at low temperatures.


#### **Features**

Dimmable with any standard MLV/Incandescent TRIAC-(Leading edge) dimmer switch Super compact ALUMINUM CASE. Class 2 UL 8750


Nema 3R - Outdoor Use

Auto-Reset Protection for short circuits & over-voltage.

FCC 15 part 2




### **Installation**





# **Specifications**

Max Load	60W
Input Voltage	120V AC
Input Current at Max Load	0.61 A
Output Voltage	12V DC
Output Current at Max Load	5 A
Power Factor	0.95
Efficiency	> 90%
Operating Temp.	-20°c - 70°c (-4°F - 158°F)
Short circuit protection	Yes
Overcurrent	Yes
Over temperature	Yes
Open circuit protection	Yes
Input Wires (White \ Black)	18 AWG
Output Wires (Red \ Black)	14 AWG
Dimensions L*W*H	6.77" x 2.67" x 1.26"
Weight	17 oz
	·



The specifications are subject to change without notice





## **Dimensions**

