



Hoffman

Screw-Cover, Type 3R

Catalog Number: A6R66
US List Price (USD): \$30.88

Bulletin Number:

- A90S3

Material:

- Steel



Model Code:

- 37980

Ship Wt. Std. Pkg. (lbs):

- 30.0

Interchangeable:

- False

IP Rating:

- IP32

Industry Standards:

UL 50, 50E Listed; Type 3R; File No. E27525 cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525 NEMA/EEMAC Type 3R IEC 60529, IP32

Description

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Description:

- Drip shield top and seam-free sides, front and back • Slip-on removable cover fastened with plated steel screws along bottom edge • Handles on larger sizes (see table) • Embossed mounting holes on back of enclosure • Knockouts in bottom of 16 and 14 gauge enclosures • Provision for padlocking • No gasketing
- See also Accessories. Industrial Corrosion Inhibitors Electric Heater Grounding Device Mounting Bracket Kit Touch-Up Paint
- ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.
- 16, 14 or 12 gauge galvanized steel
- Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Technical Data

Screw-Cover, Type 3R

Catalog Number	A6R66
A in.	6
B in.	6
C in.	6
D in.	—
Mounting H in.	2.25
Knockout Pattern	B-C-D
Body Style	A
Mounting J in.	1.06

Certifications



EU Certification



UL Certification

Documents



Instruction Manual



DOC



2D DXF CAD



3D STEP CAD



Instruction Manual



Spec Sheet



Dimension Drawing

No accessories available.