

*Hoffman*

Lay-in Painted Flat-Cover Wireway, NEMA TYPE 1 Straight Section

Catalog Number: F44T148GVP
US List Price (USD): \$58.04

Bulletin Number:

- F40FC

Material:

- Steel



Model Code:

- 36049

Ship Wt. Std. Pkg. (lbs):

- 56.0

Interchangeable:

- False

Description

Protects electrical wiring in applications where dust, dirt, oil and water are not serious problems. All sections and fittings are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Flat cover design allows for mounting flush with walls or ceilings. Keyhole screw slots on flat covers provide easy access.

Description:

Protects electrical wiring in applications where dust, dirt, oil and water are not serious problems. All sections and fittings are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Flat cover design allows for mounting flush with walls or ceilings. Keyhole screw slots on flat covers provide easy access.

Technical Data

Lay-in Painted Flat-Cover Wireway, NEMA TYPE 1 Straight Section

Catalog Number	F44T148GVP
A in.	4
B in.	4
C in.	48
Number of Knockouts .50 in.-.75 in.	—
Number of Knockouts 1.00 in.-1.25 in.	—

Certifications



EU Certification



UL Certification

Documents



Spec Sheet



2D DXF CAD



3D STEP CAD



Dimension Drawing

No accessories available.