



LU400
 400 Watt; High Pressure Sodium; Mogul Base; Et18; Clear;
 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1941

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S1941	045923019418	400	ET18	Mogul	E39	S51	LU400
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	9 5/8"	2.25"	24000	51000	2100	12	22



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

