




Catalog Number: 117TB
Item Description: 100A 7T RT OU
UPC Code: 784572100961




Brand Name: Milbank
Type: Ring Type Meter Socket
Special Features: 7 Terminal, Twin Small Closing Plates, Link Bypass, 1 Position
Application: Meter Mounting Base
Standard: UL Listed
Voltage Rating: Up to 240 Volts Alternating Current
Amperage Rating: 100 Ampere Continuous
Phase: 3 Phase
Frequency Rating: 60 Hertz
Cable Entry: Overhead and Underground
Terminal: Single Mechanical Line Side and Load Side Connector
Mounting: Surface Mount
Enclosure: Type 3R, G90 Galvanized Steel with Powder Coat Finish



Additional Specifications: Line Side Wire Range: 14 - 2/0 AWG
Load Side Wire Range: 14 - 2/0 AWG
Amperage Interrupting Current Rating or Short Circuit Current Rating: Please Contact Factory
Maximum Amperage: 100 Maximum Ampere
Number of Jaws: 7 Terminal
Hub Opening and Closing Plates: Twin Small Closing Plates
Bypass Provision: Link Bypass
Number Positions: 1 Position

Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	3	STD. MNTG. EMBOSS



Version:

1

All dimensions are +/- 1/16".
Drawing views are not to scale.
Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.