

Straight Blade Devices

15A, 250V, 2 Pole, 3 Wire Grounding

Heavy Duty Specification Grade Single Receptacle



- Features
- One-piece brass integral ground strap
 - Unique bypass contact design

Ordering Information

Description	Device Color	UPC	Catalog Number
Flush, back and side	Brown	783585013992	HBL5661


- Listings
- UL Listed to UL498 File No. E2186
Certified to CSA 22.2, No. 42 File 285
NEMA® WD-6 Compliant
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	PBT
Power Contacts	.037 in. (.9) Brass
Ground Contact	Brass
Mounting Strap	.050" (1.3) Brass
Auto Self-grounding Clip	Stainless steel
Mounting Screws	Zinc plated steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#12-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	Top: UL 94V-2, Base: UL 94V-0
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



- Online Resources
- Customer Use Drawing
 - eCatalog
 - Installation Instructions

- Accessories
- Wallplate or Weatherproof Cover 1.40" Opening

