



## Liquidtight Flexible Metal Conduit Fittings

### T&B Catalog Number:

5248

### UPC Number:

78621005248

### Status:

Active

### Description:

Liquidtight Conduit Fitting, 45 Degree 2-1/2 Inch, Non-Insulated Malleable Iron

### Features

Ability to install quickly with low torque effort

### Application

Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.

To positively bond conduit to box or enclosure.

### General

Style	Non-Insulated
Trade Size (inches)	2 1/2
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### Dimension Information

Dimension A (inches)	3 3/4
Dimension B (inches)	4 1/4
Dimension C (inches)	1

### Specifications

3dmodel	Available on Website
---------	----------------------

### Accessories & Components

Wiremesh Grips for Liquidtight Fittings	WMG-LT8
---	---------

### Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	6.21 lbs. per 100

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com